



PNEUMATIC SAMPLING PROBE 10500



Purpose : The device draws the samples from the piles and storages of hazelnut, wheat and leguminosae automatically by vacuum and stores them into the sample container which is located on the device. For wheat and other grain samples, the device can be operated by mounting a grain accessories to the device.

Technical Specifications :

- Portable device with Pneumatic Sampling
- Depending on the sample type, samples can be taken from a depth of 5-9 meters by vacuum.
- 5 aluminium pipes of 1 meter, 1 aluminium bend of 60 cm, 1 pushing-pulling apparatus, 1 pipe expanding wrench and 1 bag are supplied with the device.
- The length of the pipe is 1 m therefor it can be used even with low ceiling storages.
- The device can take in a hazelnut sample of 9 kg in one go.
- The samples can be taken seperately from the required depths by means of the device.
- Dimensions are: 900x480x380 mm, 13.5 kg. Pipe weight is excluded. 1m aluminium pipe is 1kg



Other specifications :

Volt/hz	230v - 50/60hz
Device Dimensions	
W "mm" x L "mm" x H "mm"/Weight. Kg	350 x 390 x 820mm / 21 Kg
Package Dimensions	
W "mm" x L "mm" x H "mm"/Weight. kg	45-32 x 48-56x 83-103/ 16 Kg

When you work with BASTAK you receive;

- ✓ Free technical consultancy for tailor made solutions,
- ✓ High quality instruments with free webinars and on-line trainings,
- ✓ Fast delivery of instruments, spare parts and consumables,
- ✓ Remote technical support (Audio and Video) six (6) days a week,
- ✓ Economical spare parts and consumables available in 10 years,
- ✓ Free factory visits, live tests and demos,
- ✓ On-Site Warranty and On-Site After Sales Service (for >20.000 USD orders)

“More Than 23 Years of Experience ...”

Bastak Laboratory

57 Types of Device, 35 Types of Additive



Youtube > Bastak Expert

<https://www.youtube.com/watch?v=ktEz2PHdDQg&t=10s>

Bastak Factory - 7000 m2

20.000 instruments in 142 countries



Youtube > Bastak Factory

<https://www.youtube.com/watch?v=UbtWWhEbLy4>



You can find all Catalogues and Competitor Comparison Tables in this link:

https://drive.google.com/drive/folders/1_4aXqljmlSG0Gi7c0KeMuPAGWqvi65mT



Sensitive
Nutrition



High
Efficiency



Monoblock
Study Body



Standard
Grinding



Personal
Security

*The information in this document is subject to change without any prior notice or obligation on the part of the manufacturer and should not be construed as a commitment by the manufacturer. The manufacturer assumes no responsibility for any errors that may appear in this document.