



## DRY GLUTEN 2500 (GLUTORK)



### Purpose :

The dry gluten apparatus is used in finding the final and net dry gluten values of the samples of flour and wheat.

Especially, the values of the dry gluten may be different although the wet gluten values of various wheat and flours having different water absorption are same.

### Specifications :

- The device is controlled by micro-processor.
- There are 3 warning lights on the control panel, power, test on and test off.
- There is a thermostat warning light on the device.
- The device automatically adjusts to 150° C which is the operating temperature.
- When the device reaches to 150° C, the thermostat warning light turns off.
- The device automatically stops at the end of the testing period of 4 minutes and gives out visual and audible warning.
- The heating surfaces are coated with Teflon in order to prevent the samples from adhering. There is a cover lock.

Office/ Ofis

Email : export@bastak.com.tr  
website: www.bastak.com.tr

Tel : +90 312 395 6 787  
Fax: +90 312 395 6 788

İvedik OSB 1354.Cad 1387.Sk No:19  
Yenimahalle Ankara TURKEY

Factory / Fabrika

Dağyaka mahallesi 2010 .Cd.No:23  
Kazan Ankara TURKEY

Tel : +90 312 811 2 811  
Fax: +90 312 811 2 812

Email : info@bastak.com.tr  
Website: www.bastak.com.tr



### Recommended Accessories :

- Laboratory Hammer Mill 1900 or 1800 (Used for grinding whole wheat to wheat meal)

### Other Specifications:

Volt / Hertz	230v - 50/60hz
Amper / Power	2A / 500W
Device Dimensions	
W "mm" x L "mm" x H "mm"/Weight. kg	200-80 x250-155 x 80-65mm / 3Kg
Package Dimensions	
W "mm" x L "mm" x H "mm"/Weight. kg	27 x 36 x 26 / 5Kg

### When you work with BASTAK you receive;

- ✓ Free technical consultancy for tailor made solutions,
- ✓ High quality instruments with free webinars and on-line trainings,
- ✓ Fast delivery of instruments, spare parts and consumables,
- ✓ Remote technical support (Audio and Video) six (6) days a week,
- ✓ Economical spare parts and consumables available in 10 years,
- ✓ Free factory visits, live tests and demos,
- ✓ On-Site Warranty and On-Site After Sales Service (for >20.000 USD orders)

**"More Than 23 Years of Experience ..."**

#### Bastak Laboratory

57 Types of Device, 35 Types of Additive



#### Youtube > Bastak Expert

<https://www.youtube.com/watch?v=ktEz2PHdDQg&t=10s>



#### Bastak Factory - 7000 m2

20.000 instruments in 142 countries



#### Youtube > Bastak Factory

<https://www.youtube.com/watch?v=UbtWWWhEbLy4>

You can find all Catalogues and Competitor Comparison Tables in this link:

[https://drive.google.com/drive/folders/1\\_4aXqljmISG0Gi7c0KeMuPAGWqvi65mT](https://drive.google.com/drive/folders/1_4aXqljmISG0Gi7c0KeMuPAGWqvi65mT)



Sensitive  
Nutrition



High  
Efficiency



Monoblock  
Study Body



Standard  
Grinding



Personal  
Security

\*The information in this document is subject to change without any prior notice or obligation on the part of the manufacturer and should not be construed as a commitment by the manufacturer. The manufacturer assumes no responsibility for any errors that may appear in this document.

Office/ Ofis

Email : export@bastak.com.tr  
website: www.bastak.com.tr

Tel : +90 312 395 6 787  
Fax: +90 312 395 6 788

İvedik OSB 1354.Cad 1387.Sk No:19  
Yenimahalle Ankara TURKEY

Factory / Fabrika

Dağyaka mahallesi 2010 .Cd.No:23  
Kazan Ankara TURKEY

Tel : +90 312 811 2 811  
Fax: +90 312 811 2 812

Email : info@bastak.com.tr  
Website: www.bastak.com.tr